

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Dia. X 20mm FL, VIS Coated, Hybrid Asphere



TECHSPEC® Plastic Hybrid Aspheric Lenses

Stock #66-001 CLEARANCE 3-4 DAYS

[Other Coating Options](#)



1



€99,00

ADD TO CART

Qty 1-24

€99,00

Qty 25+

€79,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 13.89
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤0.75% @425 - 675nm
Surface Quality: 60-40
Clear Aperture CA (mm): 23.00
Edge Thickness ET (mm): 3.4
Center Thickness CT (mm): 10.00 ±0.10
f/#: 0.8
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to +70
Radius R₂ (mm): 120
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 425 - 675
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View