

**TECHSPEC® 25mm Dia. x 50mm FL, YAG-BBAR Coated, Plano-Convex Lens**



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-073** ☒ In Stock

1

€160,00

ADD TO CART

Qty 1-5

€160,00

Qty 6+

€128,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.00 -0.025

**Effective Focal Length EFL (mm):**

|                                                                                                                                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------|
| 50.00 @ 587.6nm                                                                                                                               |
| <b>Back Focal Length BFL (mm):</b><br>46.00                                                                                                   |
| <b>Coating:</b><br>YAG-BBAR (500-1100nm)                                                                                                      |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 532nm<br>R <sub>abs</sub> <0.25% @ 1064nm<br>R <sub>avg</sub> <1.0% @ 500 - 1100nm |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)                                                     |
| <b>Surface Quality:</b><br>40-20                                                                                                              |
| <b>Power (P-V) @ 632.8nm:</b><br>3 Rings                                                                                                      |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>0.5 Rings                                                                                             |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                      |
| <b>Centering (arcmin):</b><br><1                                                                                                              |
| <b>Center Thickness CT (mm):</b><br>5.84 ±0.10                                                                                                |
| <b>Edge Thickness ET (mm):</b><br>2.13                                                                                                        |
| <b>Radius R<sub>1</sub> (mm):</b><br>22.92                                                                                                    |
| <b>Clear Aperture CA (mm):</b><br>24                                                                                                          |
| <b>f/#:</b><br>2                                                                                                                              |
| <b>Numerical Aperture NA:</b><br>0.25                                                                                                         |
| <b>Type:</b><br>Plano-Convex Lens                                                                                                             |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                   |
| <b>Wavelength Range (nm):</b><br>500 - 1100                                                                                                   |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns                                                         |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |