

TECHSPEC® 25mm VIS, 70R/30T, Non-Polarizing Cube Beamsplitter



Stock #13-435 3-4 DAYS

- 1 + **€258,00**

ADD TO CART

Qty 1-5
€258,00

Qty 6+
€202,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VS
Coating Specification: R _{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Ratio (R/T): 70/30
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
Ts-Tp : <6%
Absolute Transmission (%): 25 ±10
Average Transmission (%): 25 ±5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View