

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Dia. 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #88-530 3-4 DAYS



1



€166,00

ADD TO CART

Qty 1-5

€166,00

Qty 6+

€147,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) >90
Back Surface: Ground
Reflection at DWL (%) 99.9
Coating Specification: R_{abs} >99.8% @ 532nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532nm)
Design Wavelength DWL (nm): 532
Diameter (mm): 25.00 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 0-45
Substrate: Fused Silica (Coming 7980)
Damage Threshold, Reference: 10 J/cm² @532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View