

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm Dia X 125mm FL VIS 0<sup>+</sup> Coated, Illumination Grade PCX Cylinder Lens



Stock #69-730 3-4 DAYS

- 1 +

€88,00

ADD TO CART

Qty 1-5

€88,00

Qty 6+

€70,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00

Effective Focal Length EFL (mm):  
125.00

Substrate: ☐  
[N-BK7](#)

|                                                                                       |
|---------------------------------------------------------------------------------------|
| <b>f/#:</b><br>5                                                                      |
| <b>Numerical Aperture NA:</b><br>0.1                                                  |
| <b>Coating:</b><br>VIS 0° (425-675nm)                                                 |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex                                           |
| <b>Wavelength Range (nm):</b><br>425 - 675                                            |
| <b>Back Focal Length BFL (mm):</b><br>123.02                                          |
| <b>Center Thickness CT (mm):</b><br>3.00                                              |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1                                       |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                 |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2                                       |
| <b>Edge Thickness ET (mm):</b><br>1.78                                                |
| <b>Focal Length Tolerance (%):</b><br>±3                                              |
| <b>Radius R<sub>1</sub> (mm):</b><br>64.60                                            |
| <b>Surface Quality:</b><br>60-40                                                      |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |