

TECHSPEC® 25mm Dia. x 175mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-363** ☐ In Stock
[Other Coating Options](#)

1 **€118,00**

ADD TO CART

Qty 1-5
€118,00
Qty 6+
€94,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

175.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 170.84
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 9.00 ±0.20
Center Thickness CT 1 (mm): 6.00 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R ₁ (mm): 109.16
Radius R ₂ (mm): -79.38
Radius R ₃ (mm): -226.03
Edge Thickness ET (mm): 7.94
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 7.00
Numerical Aperture NA: 0.07
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View