


TECHSPEC® 25mm Diameter x 40mm EFL Aspherized Achromatic Lens



Aspherized Achromatic Lenses



Stock **#49-664** ☐ In Stock

1 **€157,00**

ADD TO CART

Qty 1-5

€157,00

Qty 6+

€125,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.05

Effective Focal Length EFL (mm):
40.00

Back Focal Length BFL (mm): 33.23
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 23.00
Centering (arcmin): ≤5
Center Thickness CT (mm): 11.58
Center Thickness CT 1 (mm): 9.00
Center Thickness CT 2 (mm): 2.58
Radius R₁ (mm): 24.80
Radius R₂ (mm): 37.60
Radius R₃ (mm): 102.34
Edge Thickness ET (mm): 7.54
Substrate: N-SK14 / N-SF57
Surface Quality: 60-40, glass surfaces only
f/#: 1.6
Numerical Aperture NA: 0.31
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Note: VIS 0° Coating on First Surface, Second Surface is Aspheric Polymer
Operating Temperature (°C): -20°C to 80°C
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View