

TECHSPEC® 25mm Dia. x 75mm FL, 532nm V-Coat, Hyperbolic Aspheric Lens



Hyperbolic Aspheric Lenses

Stock **#89-433** 3-4 DAYS

[Other Coating Options](#)



1



€240,00

ADD TO CART

Qty 1-5

€240,00

Qty 6+

€210,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00 @ 532nm

Numerical Aperture NA:

0.17
Back Focal Length BFL (mm): 75.00
Substrate: N-BK7
Aspheric Design Wavelength (nm): 532
Coating: Laser V-Coat (532nm)
Coating Specification: R _{abs} <0.25% @ 532nm
Centering (arcmin): ≤5
Surface Quality: 40-20
Clear Aperture CA (mm): 23.00
Edge Thickness ET (mm): 2.31
Center Thickness CT (mm): 4.25 ±0.1
f#: 3.00
Bevel: Protective bevel as needed
Radius R₂ (mm): 38.96
Shape of Back Surface: Convex
Type: Aspheric Lens
Conjugate Distance: Infinite
Asphere Figure Error, @ 632.8nm: 1.6λ RMS and 6λ PV
Power (diopters): 13.33

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant