

TECHSPEC®

# 25mm Dia. x -50mm FL, Uncoated, Double-Concave Lens



Stock **#32-996** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€32,50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €32,50                        |
| Qty 10+                       |
| €29,25                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                             |
|-------------------------------------------------------------|
| -50.00                                                      |
| <b>Substrate:</b> <a href="#">N-BK7</a>                     |
| <b>f#:</b><br>2.00                                          |
| <b>Numerical Aperture NA:</b><br>0.25                       |
| <b>Coating:</b><br>Uncoated                                 |
| <b>Type:</b><br>Double-Concave Lens                         |
| <b>Wavelength Range (nm):</b><br>350 - 2200                 |
| <b>Back Focal Length BFL (mm):</b><br>-50.82                |
| <b>Bevel:</b><br>Protective bevel as needed                 |
| <b>Center Thickness CT (mm):</b><br>2.50                    |
| <b>Center Thickness Tolerance (mm):</b><br>±0.10            |
| <b>Centering (arcmin):</b><br><1                            |
| <b>Clear Aperture CA (mm):</b><br>24.00                     |
| <b>Edge Thickness ET (mm):</b><br>5.40                      |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6 |
| <b>Focal Length Tolerance (%):</b><br>±1                    |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>-52.10   |
| <b>Surface Quality:</b><br>40-20                            |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                       |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |