

TECHSPEC® 25mm, f/5, Liquid Lens Cx Series Fixed Focal Length Lens



Stock **#33-661** ☐ In Stock

1

€360,00

ADD TO CART

Qty 1+

€360,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Fixed

Length (mm):
26.40

Horizontal Field of View, 1/2" Sensor:
42.0mm - 13.4°

Horizontal Field of View, 2/3" Sensor: 57.9mm - 19.1°
Filter Thread: M25.5 x0.50 with adapter #89-941
Maximum Diameter (mm): 30
Outer Diameter (mm): 30
Weight (g): 30
Horizontal Field of View, 1/3" Sensor: 31.5mm - 10.5°
Maximum Rear Protrusion (mm): 0.76
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0136
Number of Elements (Groups): 8 (7)
Note: Separate driver not included. Electronic development kit #17-123 recommended.
Horizontal Field of View, 1/1.8" Sensor: 47.3mm - 15.6°
Horizontal Field of View, 1/2.5" Sensor: 38.1mm - 12.6°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.184
Maximum Sensor Format: 2/3"
Working Distance (mm): 150 - ∞
Mount: C-Mount
Aperture (f#): f/5
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 22.94
Object Space Principal Plane (mm): 22.66
Image Space Principal Plane (mm): -13.81
Field of View at Max Sensor Format: Horizontal: 49.8mm - 19.1° Vertical: 37.2mm - 14.4° Diagonal: 62.5mm - 23.7°
Maximum Distortion (%): 0.07
Integrated Liquid Lens Model: Corning® Varioptic® A-25H0
Exit Pupil Position (mm): -13.53
Lens Wavelength Range: VIS
Imaging Lens Type: Integrated Liquid Lens to Adjust Focus Electronically
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View