

**TECHSPEC® 25mm  $\lambda$ /20, 266nm V-Coat, Nd:YAG Right Angle Prism**



TECHSPEC Nd:YAG Laser Line  $\lambda$ /20 UV Fused Silica Right Angle Prisms

Stock #37-621 3-4 DAYS



1



€384,00

ADD TO CART

Qty 1-5

€384,00

Qty 6+

€307,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):  
±15

Coating:  
Laser V-Coat (266nm)

Design Wavelength DWL (nm):  
266

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| <div><div>Substrate: <input type="checkbox"/></div><div><a href="#">Fused Silica</a> (Corning 7980)</div></div> |
| <div><div>Surface Quality:</div><div>20-10</div></div>                                                          |
| <div><div>Type:</div><div>Right Angle Prism</div></div>                                                         |
| <div><div>Dimensional Tolerance (mm):</div><div>+0.00/-0.10</div></div>                                         |
| <div><div>Bevel:</div><div>Protective bevel as needed</div></div>                                               |
| <div><div>Clear Aperture (%):</div><div>90</div></div>                                                          |
| <div><div>Length of Hypotenuse (mm):</div><div>35.40</div></div>                                                |
| <div><div>Length of Legs (mm):</div><div>25.00</div></div>                                                      |
| <div><div>Pyramid Tolerance (arcmin):</div><div>±1</div></div>                                                  |
| <div><div>Image Orientation:</div><div>Left-Handed</div></div>                                                  |
| <div><div>Coating Specification:</div><div>R<sub>abs</sub> &lt;0.25% @ 266nm</div></div>                        |
| <div><div>Surface Flatness (P-V):</div><div>λ/20</div></div>                                                    |
| <div><div>Damage Threshold, By Design: <input type="checkbox"/></div><div>3 J/cm², 20ns, 20Hz</div></div>       |

## Regulatory Compliance

|                                                                                  |
|----------------------------------------------------------------------------------|
| <div><div>RoHS 2015:</div><div><a href="#">Compliant</a></div></div>             |
| <div><div>Reach 209:</div><div><a href="#">Compliant</a></div></div>             |
| <div><div>Certificate of Conformance:</div><div><a href="#">View</a></div></div> |