

TECHSPEC® 2X, 0.13 NA, UCf Objective



Stock **#36-280** 3-4 DAYS

⊖ 1 ⊕ **€260,00**

ADD TO CART

Qty 1-2
€260,00
Qty 3+
€241,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
4.4

Horizontal Field of View, 1.1" Sensor:
7.04

Focal Length FL (mm):
10.00

Length (mm):

21.20
Magnification: 2X
Maximum Diameter (mm): 29.0
Maximum Sensor Format: 1.1"
Mount: C-Mount
Numerical Aperture NA: 0.13
Mounting Threads: C-Mount
Type: Fluorite
Resolving Power (μm): 5.12
Depth of Field (μm): 16.02
Working Distance (mm): 9.9
Weight (g): 27
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Field Number (mm): 17.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View