

TECHSPEC® 2X Cf Objective



#88-352: 2X Cf Objective

Stock #88-352 ☒ In Stock



1



€490,00

ADD TO CART

Qty 1-2

€490,00

Qty 3+

€455,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Horizontal Field of View, 2/3" Sensor:
4.40mm

Horizontal Field of View, 1.1" Sensor:
7.04

Focal Length FL (mm):
35.00

Clear Aperture CA (mm): 13.7
Coating: 425 - 675nm BBAR
Length (mm): 105.91
Magnification: 2X
Maximum Diameter (mm): 30
Maximum Sensor Format: 1.1"
Mount: C-Mount
Numerical Aperture NA: 0.120
Type: Fluorite
Resolving Power (μm): 5.55
Depth of Field (μm): 18.82
Aperture (mm): Front: 13.7
Operating Temperature (°C): +10 to +40
Working Distance (mm): 31.3
Weight (g): 95
Note: Magnification can be increased by adding tube length (see table)
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Field Number (mm): 17.6
Tube Length (mm): 50.0
Parfocal Length (mm): 83.21
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant