

TECHSPEC® 2X, 1064nm Scorpii® Nd:YAG Beam Expander



2X, 1064nm LCht Fixed YAG Beam Expander, #37-048

Stock **#37-048** 3-4 DAYS



1



€184,00

ADD TO CART

Qty 1-9

€184,00

Qty 10+

€163,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Coating:

NIR II (750-1550nm)

Design Wavelength DWL (nm):

1064

Entrance Aperture (mm): 3.5
Exit Aperture (mm): 5.2
Expansion Power: 2X
Substrate: ☐ Optical Glass
Length (mm): 20.60
Mounting Threads: M22 x0.75
Transmission (%): >96 (nominal)
Type: Beam Expander
Weight (g): 40
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/4 @ 1064nm for Input Beam ≤2.2mm (by design)
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Wavelength Range (nm): 1064
Style: Fixed Magnification
Divergence Adjustment: None

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View