

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union

SUBMIT

TECHSPEC® ZX, UV Enhanced Aluminum Canopus® Reflective Beam Expander



TECHSPEC® Canopus™ Reflective Beam Expanders



Stock #37-185 3-4 DAYS



1



€590,00

ADD TO CART

Qty 1-5

€590,00

Qty 6+

€521,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:

Enhanced Aluminum (250-700nm)
Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 4
Exit Aperture (mm): 8
Expansion Power: 2X
Substrate: ☐ Aluminum 6061-T6
Height (mm): 25.4
Length (mm): 71.00
Surface Quality: 40-20
Type: Beam Expander
Weight (g): 133
Width (mm): 38.10
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Wavelength Range (nm): 250 - 700
Style: Fixed Magnification
Surface Roughness (Angstroms): <50 RMS
Wavefront Error, P-V: ≤λ/10 on-axis for a 1mm Dia. Input Beam

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View