

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Richardson Gratings™ 300 Grooves, 25 x 25mm, 3µm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #15-773 3-4 DAYS



1



€168,00

ADD TO CART

Qty 1+

€168,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
300

Wavelength Range (nm):
1000 - 5000

Blaze Wavelength (nm):

3000 ±25
Blaze Angle (°): 26.7
Peak Efficiency, Typical (%) : 72 (2nd order)
Dimensions (mm): 25.0 x 25.0 ±0.1
Clear Aperture (%) : >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 25.00
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%) : <0.05
Polarization: S and P
Master Reference: 1156
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View