

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

30mm Dia. x 26.9mm FL, NIR I Coated, Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock #15-896 3-4 DAYS

[Other Coating Options](#)



1



€69,50

ADD TO CART

Qty 1-10

€69,50

Qty 11+

€61,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
30.00 +/-0.3

Effective Focal Length EFL (mm):
26.90 @ 587.6nm

Numerical Aperture NA:
0.56

Back Focal Length BFL (mm): 20.70
Substrate:  Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/5 x 0.63; E 0.4 Polished Side: 5/5 x 0.25; E 0.4
Clear Aperture CA (mm): 28.00
Edge Thickness ET (mm): 1.9
Center Thickness CT (mm): 10.00 ±0.20
f#: 0.90
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 30.0
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant