

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 525nm CWL, 25mm Dia, 1.2nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock #68-957 ☒ In Stock

[Additional Bandwidths](#)



1



€665,00

ADD TO CART

Qty 1-9

€665,00

Qty 10+

€585,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0 ±2

Bandwidth (nm):

1.2
OD 5 Blocking Wavelength Range (nm) : 291 - 321.8 & 328.3 - 380.7
OD 6 Blocking Wavelength Range (nm): 299 - 320.1 & 329.9 - 357.5
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 21.00
Center Wavelength CWL (nm): 325.00
Design Wavelength DWL (nm): 325
Full Width-Half Max FWHM (nm): 2.30
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.0/-0.1
Transmission (%): ≥80
Type: Bandpass Filter
Durability: Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A, sect. 3.4.1
Transmitted Wavefront, RMS: λ/4 @ 633nm
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View