

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

Conerent® USB Powermax Pro Measurement System 1315456 | 350W

See More by [Coherent®](#)



Coherent USB-PowerMax Pro Fast Measurement Systems

Stock #37-076 3-4 DAYS

- 1 + €4.550,00

ADD TO CART

Qty 1+

€4.550,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Model Number:
1315456

Type:
Meterless

Length of Cable (m):
4.2

Active Area (mm):
25 Dia.

Computer Interface: USB
Rise Time (μs): ≤10
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 810
Spectral Compensation Accuracy (%): ±5
Cooling Method: Water/Air (intermittent)
Maximum Incident Power Density (kW/cm²): 50
Fall Time (μs): ≤10
Wavelength Range (nm): 700 - 1070, 10600
Power Range (Water-Cooled): 3W to 350W
Maximum Incident Energy Density: 30J/cm² (3ns; 755nm)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View