

TECHSPEC® 350nm CWL, 25mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock **#39-184** 3-4 DAYS

[Additional Bandwidths](#)



1



€263,00

ADD TO CART

Qty 1-5

€263,00

Qty 6+

€206,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Optical Density OD (Average):

≥4.0
Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 350.00 ±2.0
Full Width-Half Max FWHM (nm): 10.00 ±2.0
Full Width-Half Max FWHM Tolerance (nm): ±2.0
Substrate:  Fused Silica (Corning 7980)
Minimum Transmission (%): >50
Coating: Hard Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: General Filtering
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Mount Thickness (mm): 5.0 ±0.1
Substrate Thickness (mm): 3.5 ±0.5 typical

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant