

355 & 532nm, 6-9mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal π Shaper_NUV_Q-7.5

See More by [AdlOptica](#)



Stock #12-239 3-4 DAYS

- 1 + **€3.356,00**

ADD TO CART

Qty 1-4
€3.356,00

Qty 5+
€3.019,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
20

Design Wavelength DWL (nm): 355, 532
Diameter (mm): 42.00
Model Number: πShaper_NUV_Q-7.5
Length (mm): 29.00
Transmission (%): >99
Type: Beam Shaper
Weight (g): 50
Wavelength Range (nm): 335 - 560
Input Beam Diameter, 1/e² (mm): 6 - 9
Maximum Input Power, CW (kW): 0.2
Inner Thread: M30 x 0.75
Outer Thread: M30 x 0.75
Compatible Adapter: #12-322
Input Beam Mode: TEM ₀₀
Typical Input Beam Mode Quality, M²: <1.5
Input Beam Divergence (mrad): ±20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant