

TECHSPEC® 355nm CWL, 12.5mm Dia,1.3nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock **#68-927** ☐ In Stock

[Additional Bandwidths](#)



1



€332,00

ADD TO CART

Qty 1-9

€332,00

Qty 10+

€292,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0 ±2

Bandwidth (nm):

1.3
OD 5 Blocking Wavelength Range (nm) : 314.8 - 351.8 & 358.6 - 422.5
OD 6 Blocking Wavelength Range (nm): 326.6 - 349.7 & 360.3 - 390.5
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 8.5
Center Wavelength CWL (nm): 355.00
Design Wavelength DWL (nm): 355
Full Width-Half Max FWHM (nm): 2.50
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.0/-0.1
Transmission (%): ≥80
Type: Bandpass Filter
Durability: Environmental: MIL-STD-810F, sect. 507.4 Durability: MIL-C-48497A, sect. 3.4.1
Transmitted Wavefront, RMS: λ/4 @ 633nm
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View