

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Precision Ultraviolet Mirrors

Stock #18-730 3-4 DAYS



1



€289,00

ADD TO CART

Qty 1-5

€289,00

Qty 6+

€231,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
35.00 +0.0/-0.2

Surface Flatness (P-V):
λ/10

Substrate: ☐

Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} ≥78% @ 120 - 125nm R _{avg} ≥85% @ 120 - 600nm
Coating: Enhanced Aluminum (120-600nm)
Coating Type: Metal
Angle of Incidence (°): 0
Clear Aperture (%): 90
Design Wavelength DWL (nm): 120
Parallelism (arcsec): <30
Thickness (mm): 5.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 120 - 600
Vacuum Compatibility: 10 ⁻⁷ Torr

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View