

**TECHSPEC® 3.5mm, f/4 Cr Series Fixed Focal Length Lens**



3.5mm Cr Series Fixed Focal Length Lens

Stock **#37-394** ☐ In Stock



1



**€485,00**

ADD TO CART

Qty 1+

€485,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Iris Option:**  
Fixed

**Length (mm):**  
39.01

**Horizontal Field of View, 1/2" Sensor:**  
29.5mm - 87.2°

**Filter Thread:**  
M105 x 1.00 with required adapter [#89-848](#)

**Weight (g):**

|                                                                                                                              |
|------------------------------------------------------------------------------------------------------------------------------|
| 120                                                                                                                          |
| <b>Horizontal Field of View, 1/3" Sensor:</b><br>23.0mm - 74.4°                                                              |
| <b>Maximum Image Circle (mm):</b><br>9.00                                                                                    |
| <b>Horizontal Field of View @ Max Sensor Format:</b><br>41.2mm - 102.8°                                                      |
| <b>Number of Elements (Groups):</b><br>8 (7)                                                                                 |
| <b>Horizontal Field of View, 1/1.8" Sensor:</b><br>41.2mm - 102.8°                                                           |
| <b>Front Thread:</b><br>M50.0 x0.5 (Male)                                                                                    |
| <b>Type:</b><br>Fixed Focal Length Lens                                                                                      |
| <b>Diameter (mm):</b><br>33.80                                                                                               |
| <b>Focal Length FL (mm):</b><br>3.50                                                                                         |
| <b>Maximum Sensor Format:</b><br>1/1.8"                                                                                      |
| <b>Working Distance (mm):</b><br>0 - ∞                                                                                       |
| <b>Mount:</b><br>C-Mount                                                                                                     |
| <b>Aperture (f/#):</b><br>f/4                                                                                                |
| <b>Coating:</b><br>425 - 675nm BBAR                                                                                          |
| <b>Horizontal Field of View, 1/4" Sensor:</b><br>16.3mm - 57.4°                                                              |
| <b>Lens Wavelength Range:</b><br>VIS                                                                                         |
| <b>Storage Temperature (°C):</b><br>-20 to +60 For questions regarding operating temperature please contact our support team |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |