

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 38.1mm Dia., 6.35mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock #38-912 3-4 DAYS



1



€197,50

ADD TO CART

Qty 1-5

€197,50

Qty 6+

€178,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):  
34.29

Coating:  
Uncoated

Diameter (mm):  
38.10 +0.00/-0.10

|                                                                                    |
|------------------------------------------------------------------------------------|
| <div>Substrate: <div><div></div></div><div>Fused Silica (Corning 7980)</div></div> |
| <div>Index of Refraction <math>n_d</math>:<br/>1.458</div>                         |
| <div>Surface Quality:<br/>10-5</div>                                               |
| <div>Thickness (mm):<br/>6.35 ±0.20</div>                                          |
| <div>Type:<br/>Laser Window Substrate</div>                                        |
| <div>Parallelism (arcmin):<br/>&lt;3</div>                                         |
| <div>Bevel:<br/>Protective as needed</div>                                         |
| <div>Clear Aperture (%):<br/>90</div>                                              |
| <div>Abbe Number (<math>v_d</math>):<br/>67.8</div>                                |
| <div>Wavelength Range (nm):<br/>200 - 2200</div>                                   |
| <div>Surface Flatness (P-V):<br/>λ/10</div>                                        |
| <div>Fused Silica Grade:<br/>7980 0F</div>                                         |
| <div>Edges:<br/>Fine Ground</div>                                                  |
| <div>Type of Window:<br/>Glass</div>                                               |

## Regulatory Compliance

|                                                 |
|-------------------------------------------------|
| <div>RoHS 2015:<br/>Compliant</div>             |
| <div>Reach 219:<br/>Compliant</div>             |
| <div>Certificate of Conformance:<br/>View</div> |