


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

38.1mm Dia., 5 Arcsec, Bare Gold Replicated Hollow Metal Retroreflector



Replicated Hollow Metal Retroreflectors

Stock #15-903 [CONTACT US](#)



1



€600,00

ADD TO CART

Qty 1-9

€600,00

Qty 10+

€540,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcsec):
5

Clear Aperture CA (mm):
35.56

Coating:
Bare Gold

Diameter (mm): 38.10
Substrate: Aluminum
Height (mm): 39.64
Surface Quality: 60-40
Mounting Threads: 10-24
Type: Retroreflector
Dimensional Tolerance (mm): +0.025/-0.051
Image Orientation: Left-Handed
Coating Specification: R_{avg} >94% @ 700 - 800nm R_{avg} >97% @ 800 - 2000nm R_{avg} >98% @ 2 - 12μm
Ray Deviation (°): 180
Wavelength Range (nm): 700 - 12000
Style: Standard Profile

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View