

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 38.1mm Dia., 6.35mm Thick, 980nm, N/10 Fused Silica Window



TECHSPEC N/10 Laser Line Coated Windows

Stock #39-707 3-4 DAYS



1



€217,50

ADD TO CART

Qty 1-5

€217,50

Qty 6+

€174,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
34.29

Coating:
Laser V-Coat (980nm)

Design Wavelength DWL (nm): 980
Diameter (mm): 38.10 +0.00/-0.10
Substrate: Fused Silica (Coming 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Coating Specification: R_{abs} <0.25% @ 980nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 15 J/cm² @ 980nm, 20ns, 20Hz
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View