

38.4mm Diameter x 30mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-538** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕

€57,00

ADD TO CART

Qty 1-10
€57,00
Qty 11+
€50,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
38.40 +0.2/-0.4

Effective Focal Length EFL (mm):
30.00

Numerical Aperture NA:
0.64

Substrate: B270
Focal Length Tolerance (%) : ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin) : ≤25
Surface Quality: 80-50 (typical)
Center Thickness CT (mm) : 19.00 ±0.25
f/#: 0.78
Bevel: Protective bevel as needed
Radius R₂ (mm) : 84.125
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm) : 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant