

TECHSPEC®

387nm CWL, 25mm Dia, 11nm Bandwidth, Unmounted OD 6 Fluorescence Bandpass Filter



Stock #18-386 3-4 DAYS

[Additional Bandwidths](#)

⊖ 1 ⊕ **€312,00**

ADD TO CART

Qty 1-5

€312,00

Qty 6+

€261,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00 ±0.1

Angle of Incidence (°):  
0 ±5

|                                                                                                                                                                                  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Bandwidth (nm):</b><br>11.00                                                                                                                                                  |
| <b>OD 6 Blocking Wavelength Range (nm):</b><br>405 - 700                                                                                                                         |
| <b>Optical Density OD (Average):</b><br>≥6.0                                                                                                                                     |
| <b>Clear Aperture CA (mm):</b><br>22.50                                                                                                                                          |
| <b>Center Wavelength CWL (nm):</b><br>387.00                                                                                                                                     |
| <b>Full Width-Half Max FWHM (nm):</b><br>15.00                                                                                                                                   |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Coming 7980)                                                                                         |
| <b>Minimum Transmission (%):</b><br>90                                                                                                                                           |
| <b>Coating:</b><br>Hard Coated                                                                                                                                                   |
| <b>Surface Quality:</b><br>60-40                                                                                                                                                 |
| <b>Thickness (mm):</b><br>2.00 ±0.1                                                                                                                                              |
| <b>Type:</b><br>Bandpass Filter                                                                                                                                                  |
| <b>Blocking Wavelength Range (nm):</b><br>250 -1050                                                                                                                              |
| <b>Construction:</b><br>Unmounted                                                                                                                                                |
| <b>Transmitted Wavefront, RMS:</b><br>λ/4 (prior to coating)                                                                                                                     |
| <b>Compatible Fluorophore:</b><br>DAPI Excitation / BFP & CFP Excitation                                                                                                         |
| <b>Environmental Durability:</b><br>Humidity per ML-STD-810H, Section 507.6<br>Temperature per ML-STD-810H, Section 501.7 and 502.7                                              |
| <b>Physical Durability:</b><br>Adhesion per ML-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11<br>Cleaning per ML-C-48497A Section 4.5.4.2 |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |