

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 394nm CWL, 25mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock #65-131 3-4 DAYS



1



€263,00

ADD TO CART

Qty 1-5

€263,00

Qty 6+

€206,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm): 21.0
Center Wavelength CWL (nm): 394.00 ±2.0
Full Width-Half Max FWHM (nm): 10.00 ±2.0
Full Width-Half Max FWHM Tolerance (nm): ±2.0
Substrate: ☐ Optical Glass
Minimum Transmission (%): ≥85
Coating: Hard Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: mBBR+GSH Absorption
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 5.0 ±0.1
Substrate Thickness (mm): 3.5 ±0.5 typical

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant