

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 3X, 1064nm Vega® Nd:YAG Laser Line Beam Expander



3X, 1064nm DABeam Expander, #35-099

Stock #35-099 3-4 DAYS



1



€360,00

ADD TO CART

Qty 1-9

€360,00

Qty 10+

€317,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Entrance Aperture (mm): 8
Exit Aperture (mm): 23
Expansion Power: 3X
Substrate: ☐ Fused Silica (Corning 7980)
Length (mm): 80.90
Mounting Threads: Input: Male M30 x 1 Output: Female M27 x 0.5 (not intended for use)
Transmission (%): >99 (nominal)
Type: Beam Expander
Weight (g): 76
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/10 for 4mm input beam (nominal, λ = DWL)
Coating Specification: R _{abs} <0.25% @ 1064nm
Wavelength Range (nm): 1000 - 1140
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 10 J/cm² @ 1064nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View