


TECHSPEC® 3X, Bare Gold Canopus® Reflective Beam Expander



TECHSPEC® Canopus™ Reflective Beam Expanders



Stock **#37-190** 3-4 DAYS

- 1 + **€630,00**

ADD TO CART

Qty 1-5
€630,00
Qty 6+
€556,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:

Bare Gold
Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 4
Exit Aperture (mm): 12
Expansion Power: 3X
Substrate: ☐ Aluminum 6061-T6
Height (mm): 25.4
Length (mm): 72.60
Surface Quality: 40-20
Type: Beam Expander
Weight (g): 117
Width (mm): 38.10
Coating Specification: R _{avg} >94% @ 700 - 800nm R _{avg} >97% @ 800 - 2000nm R _{avg} >98% @ 2 - 12μm
Wavelength Range (nm): 700 - 12000
Style: Fixed Magnification
Surface Roughness (Angstroms): <50 RMS
Wavefront Error, P-V: ≤λ/10 on-axis for a 1mm Dia. Input Beam

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View