

TECHSPEC® 3X, Ultrafast-Enhanced Silver Canopus® Reflective Beam Expander



TECHSPEC® Canopus™ Reflective Beam Expanders



Stock **#13-074** [CONTACT US](#)

- 1 + **€619,00**

ADD TO CART

Qty 1-5
€619,00
Qty 6+
€545,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:

Ultrafast-Enhanced Silver
Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 4
Exit Aperture (mm): 12
Expansion Power: 3X
Substrate: ☐ Aluminum 6061-T6
Height (mm): 25.4
Length (mm): 72.68
Surface Quality: 40-20
Type: Beam Expander
Weight (g): 117
Width (mm): 38.10
Coating Specification: R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ 730 - 870nm, 45°
Wavelength Range (nm): 600 - 1050
Style: Fixed Magnification
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 800nm, 48fs, 100Hz, 1 pulse (typical) 0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)
Surface Roughness (Angstroms): <50 RMS
Wavefront Error, P-V: ≤λ/10 on-axis for a 1mm Dia. Input Beam
GDD Specification: 0 ±20fs² @ 600 - 1050nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View