

TECHSPEC®

3mm Dia. x 6mm FL, NIR II Coated, Double-Convex Lens



Stock **#67-592** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€62,50

ADD TO CART

Qty 1-9
€62,50
Qty 10+
€56,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Back Focal Length BFL (mm):

5.37
Effective Focal Length EFL (mm): 6.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Center Thickness CT (mm): 1.80
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.41
Radius R ₁ =R ₂ (mm): 5.88
Clear Aperture CA (mm): 2.5
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant