

4.00µm CWL, 25.0mm Diameter, 2.0 FWHM, IR Bandpass Filter



Stock #11-998 [CONTACT US](#)

-

1

+

€433,00

ADD TO CART

Qty 1-9
€433,00
Qty 10+
€390,20
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm):

21.0
Center Wavelength CWL (nm): 4,000.00 ±200
Full Width-Half Max FWHM (nm): 2,000.00
Substrate: ☐ Silicon (Si)
Coating: Traditional Coated
Surface Quality: 60-40
Thickness (mm): 1.00 ±0.2
Transmission (%): 80 (minimum)
Type: Bandpass Filter
Typical Applications: SWIR
Blocking Wavelength Range (nm): 200 - 7000
Center Wavelength CWL (μm): 4.00 ±0.20
Full Width-Half Max FWHM (μm): 2.00 ±0.20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant