

## 400µm Aperture Diameter, Mounted, Precision Pinhole



400µm Aperture Diameter, Mounted, Precision Pinhole, #56-286

Stock #56-286  In Stock

⊖ 1 ⊕ **€75,00**

**ADD TO CART**

Qty 1-5

€75,00

Qty 6+

€66,20

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Mounted

Outer Diameter (mm):  
25 +0.4/-0.000

Construction:  
Stainless Steel

Fixed Aperture Diameter (µm):  
400

Thickness (mm):  
0.03 Nominal

Aperture Tolerance (µm):  
±5

Mount Thickness (mm):  
1.25 ±0.05

Aperture Centration (µm):  
±125

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 235:  
[Compliant](#)

---