


400nm, 12.5mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock **#15-465** ☐ In Stock

-

1

+

€82,00

ADD TO CART

Qty 1-9
€82,00
Qty 10+
€73,80
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads	
Diameter (mm): 12.50 +0.00/-0.20 Angle of Incidence (°): 0 Optical Density OD (Average): ≥2.0	

Cut-Off Wavelength (nm): 400.00 ±8
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 420 - 505
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 325 - 385
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 325 - 505

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View