


**TECHSPEC® 40mm Dia. x 200mm FL, YAG-BBAR Coated, Achromatic Lens**



YAG-BBAR Coated Achromatic Lenses



Stock **#11-733** 3-4 DAYS

[Other Coating Options](#)



1



€166,00

ADD TO CART

Qty 1-5

€166,00

Qty 6+

€132,75

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
40.00 +0.000/-0.025

|                                                                                                                                               |
|-----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Effective Focal Length EFL (mm):</b><br>200.00                                                                                             |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                                                      |
| <b>Back Focal Length BFL (mm):</b><br>194.14                                                                                                  |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                                                                   |
| <b>Clear Aperture CA (mm):</b><br>39.00                                                                                                       |
| <b>Centering (arcmin):</b><br><1                                                                                                              |
| <b>Center Thickness CT (mm):</b><br>12.50 ±0.20                                                                                               |
| <b>Center Thickness CT 1 (mm):</b><br>8.50 ±0.10                                                                                              |
| <b>Center Thickness CT 2 (mm):</b><br>4.00 ±0.10                                                                                              |
| <b>Radius R<sub>1</sub> (mm):</b><br>124.12                                                                                                   |
| <b>Radius R<sub>2</sub> (mm):</b><br>-87.26                                                                                                   |
| <b>Radius R<sub>3</sub> (mm):</b><br>-253.10                                                                                                  |
| <b>Edge Thickness ET (mm):</b><br>10.09                                                                                                       |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a> / <a href="#">N-SF5</a>                                                   |
| <b>Surface Quality:</b><br>40-20                                                                                                              |
| <b>f/#:</b><br>5.00                                                                                                                           |
| <b>Numerical Aperture NA:</b><br>0.10                                                                                                         |
| <b>Coating:</b><br>YAG-BBAR (500-1100nm)                                                                                                      |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 532nm<br>R <sub>abs</sub> <0.25% @ 1064nm<br>R <sub>avg</sub> <1.0% @ 500 - 1100nm |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                         |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                   |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                                   |
| <b>Type:</b><br>Achromatic Lens                                                                                                               |
| <b>Wavelength Range (nm):</b><br>500 - 1100                                                                                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |