

TECHSPEC® 40mm Dia., 0.80 Numerical Aperture NIR Coated, Aspheric Lens



Stock **#67-261** 3-4 DAYS

[Other Coating Options](#)



1



€595,00

ADD TO CART

Qty 1-5

€595,00

Qty 6+

€476,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Numerical Aperture NA:

0.80
Back Focal Length BFL (mm): 15.73
Substrate: N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 36
Edge Thickness ET (mm): 1.49
Center Thickness CT (mm): 15.50 ±0.1
f/#: 0.63
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 40.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant