

TECHSPEC® 40mm Dia. x 300mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-385** ☐ In Stock
[Other Coating Options](#)

1 **€180,00**

ADD TO CART

Qty 1-5
€180,00
Qty 6+
€144,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

300.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 293.63
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 39.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 13.10 ±0.20
Center Thickness CT 1 (mm) : 9.00 ±0.10
Center Thickness CT 2 (mm) : 4.10 ±0.10
Radius R₁ (mm) : 194.96
Radius R₂ (mm) : -148.27
Radius R₃ (mm) : -483.71
Edge Thickness ET (mm) : 11.66
Substrate: ☐ N-BAK4 / N-SF10
Surface Quality : 40-20
f/# : 7.5
Numerical Aperture NA : 0.07
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View