

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 40mm Dia. X 60mm FL, VIS 0<sup>+</sup> Coated, Achromatic Lens



Stock #47-737 3-4 DAYS

[Other Coating Options](#)



1



€168,00

ADD TO CART

Qty 1-5

€168,00

Qty 6+

€134,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                |
|----------------------------------------------------------------|
| 60.00                                                          |
| Focal Length Tolerance (%):<br>±1                              |
| Back Focal Length BFL (mm):<br>50.29                           |
| Focal Length Specification Wavelength (nm):<br>587.6           |
| Clear Aperture CA (mm):<br>39.00                               |
| Centering (arcmin):<br><1                                      |
| Center Thickness CT (mm):<br>17.46 ±0.20                       |
| Center Thickness CT 1 (mm):<br>14.46 ±0.10                     |
| Center Thickness CT 2 (mm):<br>3.00 ±0.10                      |
| Radius R <sub>1</sub> (mm):<br>37.33                           |
| Radius R <sub>2</sub> (mm):<br>-31.54                          |
| Radius R <sub>3</sub> (mm):<br>-124.51                         |
| Edge Thickness ET (mm):<br>10.03                               |
| Substrate: <a href="#">N-SK11</a> / <a href="#">N-SF5</a>      |
| Surface Quality:<br>40-20                                      |
| f/#:<br>1.5                                                    |
| Numerical Aperture NA:<br>0.33                                 |
| Coating:<br>VIS 0° (425-675nm)                                 |
| Coating Specification:<br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm |
| Power (P-V) @ 632.8nm:<br>1.5λ                                 |
| Irregularity (P-V) @ 632.8nm:<br>λ/4                           |
| Bevel:<br>Protective bevel as needed                           |
| Type:<br>Achromatic Lens                                       |
| Wavelength Range (nm):<br>425 - 675                            |

### Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Reach 219:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |