

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

42mm Radius, ±10° Tilt, Micro Manual Goniometer



Micro Manual Goniometers

Stock #13-780 [CONTACT US](#)



1



€2.476,00

ADD TO CART

Qty 1+

€2.476,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm):
66 x 19.1

Travel (°):

±10
Thickness (mm): 17.50
Leadscrew Pitch (mm): 0.32
Load Capacity, Normal (kg): 0.45
Mounting Threads: (10) 0-80
Radius R (mm): 42
Stage Size (inches): 2.6 x 0.75
Weight (g): 40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View