

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 4.5mm Dia. X 4.5mm FL, VIS-EXT Coated Plano-Convex Lens



Stock #88-627 3-4 DAYS

[Other Coating Options](#)

- 1 +

€67,00

ADD TO CART

Qty 1-9
€67,00

Qty 10+
€60,25

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
4.50 +0.0/-0.025

Effective Focal Length EFL (mm):

4.50 @ 587.6nm
Back Focal Length BFL (mm): 3.05
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-LASF44
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 2.59 ±0.05
Edge Thickness ET (mm): 1.8
Radius R₁ (mm): 3.61
Clear Aperture CA (mm): 4.05
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant