

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 4mm Dia. 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #12-627

CONTACT US



1



€114,00

ADD TO CART

Qty 1-5

€114,00

Qty 6+

€101,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin): <3
Clear Aperture (%): 90
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 532nm
Wavelength Range (nm): 523 - 537
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532nm)
Design Wavelength DWL (nm): 532
Diameter (mm): 4.00 +0.00/-0.10
Thickness (mm): 3.00 ±0.20
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View