

50 x 50mm, 0.4mm Thick, SCHOTT D263® T eco Window

See More by [SCHOTT Optical Components](#)



Stock #18-302 3-4 DAYS

⊖ 1 ⊕ **€36,00**

ADD TO CART

Qty 1-5
€36,00
Qty 6+
€29,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
45.00 x 45.00

Dimensions (mm): 50.00 x 50.00 ±0.25
Thickness (mm): 0.40 ±0.05
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.2 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Cut and Seamed
Index of Refraction n_d: 1.523
Poisson's Ratio: 0.21
Substrate: D263@Teco
Surface Quality: 80-50
Transformation Temperature (°C): 557
Type: Protective Window
Wavelength Range (nm): 350 - 2000
Young's Modulus (GPa): 72.9
Length (mm): 50.00
Width (mm): 50.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant