

TECHSPEC® 50.8mm Dia., 532nm, λ/10 Ultra-Low Reflectivity Window



λ/10 Ultra-Low Reflectivity Windows

Stock **#11-266** CLEARANCE 3-4 DAYS



1



€199,95

ADD TO CART

Qty 1+

€199,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture CA (mm):
45.72

Coating:
Laser Ultra V-Coat (532nm)

Coating Specification: R_{abs} <0.10% @ 532nm
Diameter (mm): 50.80 +0.00/-0.10
Thickness (mm): 9.53 ±0.20
Design Wavelength DWL (nm): 532
Parallelism (arcmin): <3
Substrate: Fused Silica (Corning 7980)
Fused Silica Grade: 7980 0F
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Type: Laser Line Window
Young's Modulus (GPa): 73
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Index of Refraction n_d: 1.458
Poisson's Ratio: 0.16
Abbe Number (v_d): 67.8
Edges: Fine Ground
Damage Threshold, By Design: ☐ 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View