

50mW, 808nm Fiber-Coupled Laser Module



Stock **#19-484** [CONTACT US](#)

- 1 + **€600,00**

ADD TO CART

Qty 1-9
€600,00

Qty 10+
€535,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
+15 to +30

Operating Voltage (V):
5.0

Output Power (mW):

50
Spatial Mode: Fiber-Coupled
Wavelength (nm): 808.00 ±5
Length of Fiber (m): 1
Type of Laser: Diode
Laser Class - CDRH: Class IIIb
Color: Infrared
Connector: SMA
Length (mm): 151.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant