

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50.8mm Dia. x 500mm EFL, 355nm U-45°, Concave Laser Line Mirror



Laser Line Concave Mirrors

Stock #11-336 3-4 DAYS



1



€237,00

ADD TO CART

Qty 1-4

€237,00

Qty 5+

€213,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Design Wavelength DWL (nm):
355

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Diameter (mm): 50.80 +0.00/-0.20
Effective Focal Length EFL (mm): 500.00
Radius of Curvature (mm): 1,000.00
Coating: Laser Mirror (355nm)
Coating Specification: R_{abs} >99.80% @ 355nm (0-45° AOI)
Coating Type: Dielectric
Back Surface: Fine Grind
Center Thickness CT (mm): 9.68
Clear Aperture (%): 90
Edge Thickness ET (mm): 10.00 ±0.20
Radius R₁ (mm): 1,000.00
Type: Concave Mirror
Wavelength Range (nm): 351 - 358
Irregularity (P-V) @ 632.8nm: 3λ/20
Damage Threshold, Reference: 1 MW/cm² @ 355nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View