

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50mm Dia., 6mm Thick, YAG-BBAR Coated, M4 N-BK7 Window



Stock #13-328 3-4 DAYS



1



€124,50

ADD TO CART

Qty 1-5

€124,50

Qty 6+

€99,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number ( $v_d$ ):  
64.17

Bevel:  
Protective as needed

Clear Aperture (%):  
90

|                                                                                                                                                            |
|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>Clear Aperture CA (mm):<br/>45.00</div>                                                                                                               |
| <div>Diameter (mm):<br/>50.00 +0.0/-0.25</div>                                                                                                             |
| <div>Thickness (mm):<br/>6.00 ±0.20</div>                                                                                                                  |
| <div>Coating:<br/>YAG-BBAR (500-1100nm)</div>                                                                                                              |
| <div>Coating Specification:<br/>R<sub>abs</sub> &lt;0.25% @ 532nm<br/>R<sub>abs</sub> &lt;0.25% @ 1064nm<br/>R<sub>avg</sub> &lt;1.0% @ 500 - 1100nm</div> |
| <div>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):<br/>7.1 (-30 to +70°C)<br/>8.3 (+20 to +300°C)</div>                                       |
| <div>Density (g/cm³):<br/>2.51</div>                                                                                                                       |
| <div>Edges:<br/>Fine Ground</div>                                                                                                                          |
| <div>Index of Refraction n<sub>d</sub>:<br/>1.516</div>                                                                                                    |
| <div>Knoop Hardness (kg/mm²):<br/>610</div>                                                                                                                |
| <div>Parallelism (arcmin):<br/>&lt;1</div>                                                                                                                 |
| <div>Poisson's Ratio:<br/>0.206</div>                                                                                                                      |
| <div>Substrate:<br/><a href="#">N-BK7</a></div>                                                                                                            |
| <div>Surface Flatness (P-V):<br/>λ/4</div>                                                                                                                 |
| <div>Surface Quality:<br/>60-40</div>                                                                                                                      |
| <div>Type:<br/>Protective Window</div>                                                                                                                     |
| <div>Wavelength Range (nm):<br/>500 - 1100</div>                                                                                                           |
| <div>Young's Modulus (GPa):<br/>82</div>                                                                                                                   |
| <div>Damage Threshold, By Design: <input type="checkbox"/><br/>5 J/cm² @ 532nm, 10ns</div>                                                                 |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
| <div>Reach 235:<br/><a href="#">Compliant</a></div>             |