

TECHSPEC®

600-1000nm, 50.8mm Dia. x 500mm EFL, Ultrafast-Enhanced Silver Concave Laser Mirror



TECHSPEC® Ultrafast-Enhanced Silver Concave Laser Mirrors

Stock #13-072 3-4 DAYS



1



€253,00

ADD TO CART

Qty 1-5

€253,00

Qty 6+

€224,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ [Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):

50.80 +0.00/-0.20
Effective Focal Length EFL (mm): 500.00
Radius of Curvature (mm): 1,000.00
Coating: Ultrafast-Enhanced Silver (600-1000nm)
Coating Specification: R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ 730 - 870nm, 45°
GDD Specification: 0 ±20fs ² @ 600 - 1050nm
Coating Type: Ultrafast-Enhanced Silver
Clear Aperture (%) : 80
Edge Thickness ET (mm): 10.00 ±0.20
Type: Concave Mirror
Wavelength Range (nm): 600 - 1000
Irregularity (P-V) @ 632.8nm: 0.15λ
Damage Threshold, Reference: ☐ 0.3 J/cm ² @ 800nm, 48fs, 1 pulse (typical) 0.16 J/cm ² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View